# Specification S-25A80-Gx/CXP Issue 2.0



#### Key characteristics



- OnSemi PYTHON25k sensor
- True Global Shutter CMOS
- Monochrome and Color
- Dark and bright uniformity corrections
- Multiple Low Frequency Flat Field Correction sets
- CXP-3 DIN 2/4 and CXP-6 DIN 1/2/4 configurable
- M12 I/O connector
- CoaXPress V1.1.1 compliant
- CoaXPress V1.0 compatible

#### Introduction

The Sapphire 25 Mpx CoaXPress camera delivers 5120x5120 pixel resolution at 84+ fps with 4.5 micron square pixels. Adimec offers the Sapphire 25 Mpx CXP cameras in a low power, compact outline design without forced cooling through a fan. This provides optimal design freedom for integrating optics and placement in inspection tools.

Global non-uniformities in the scene due to optics or lightning can be corrected via the Low Frequency Flat Field Correction. Multiple LF FFC sets are supported to compensate for various system lightning or optics conditions.

Similar to our Q-12A180, the Sapphire is based on Adimec's new second generation CoaXPress V1.1.1 compliant 25 Gb/s CoaXPress Quad interface. This interface is also fully backward compatible to existing V1.0 frame grabbers.




#### **Performance**

Туре	ON Semiconductor PYTHON25K		
Architecture	CMOS Progressive scan Global Shutter (PLS 1/5000)		
Optical format	35 mm		
Pixel size	4.5 μm x 4.5 μm		
Active pixels	5120 (H) x 5120 (V)		
Microlenses	Yes		
Dynamic range	59 dB*	57 dB**	
Full well	12 ke <sup>-</sup> *	10 ke <sup>· **</sup>	
Dark noise	14 e <sup>-*</sup>	14 e <sup>- **</sup>	
Sensitivity mono	30 LSB10		

<sup>\*</sup> Sensor specification
\*\* Typical value

### **Quantum Efficiency**



### **Functionality**

Image acquisition	Continuous / Controlled		
Integration time control	Programmable between 32 $\mu s$ and 100 ms in steps of 1 $\mu s$		
Gain	Digital fine gain selectable between 1x and 32x in steps of 0.001		
Video Processing	Automatic black level control loop – Manual/One push White Balance – User programmable Look Up Table in output stream (10 bit)		
Region of interest	Size and position programmable Region of Interest (ROI) – Increased frame speed via ROI – Multiple band ROI readout - Digital Binning - Subsampling		
Defect pixel correction	On/Off switchable - Readout and editing of defect pixel map - Factory calibrated		
Test mode	Internal test pattern generator available for checking of the complete digital image chain		
Mirroring	The output can be reversed in the horizontal and vertical direction		
Uniformity correction	Up to 50 low frequency flat field correction sets can be saved in non-volatile memory (Mono only) – Up to 18 out of 50 can be live switched from frame to frame (Mono only) User calibratable dark field and bright field uniformity correction		
Miscellaneous functions	Programmable I/O polarity – 1 factory set and 1 user set for storage of camera settings – Camera type, but state and serial number can be read via software		

## Interfacing

١/	ı	М		0
v	ı	u	ᆫ	u

Video output	CoaxPress V1.1.1 /1.0 CXP-3 DIN 2/4 and CXP-6 DIN 1/2/4 configurable		
External Sync	I/O or CXP controlled		
Output resolution	8 / 10 bit		
Connector	4 x DIN1.0/2.3 (Figure 1)		
Camera Control Prote	ocol		
Interface	GenlCam via CoaxPress		
Throughput	20Mbps		
Protocol	GenTL		
I/O			
Output	Fully programmable flash strobe signal (duration, delay and polarity)		
Input	Trigger signal with programmable polarity		
Connector	M12 Binder 09-3432-216-04 (figure 2)		
Power			
Input voltage	24Vdc PoCXP		
Power dissipation	<9.5W @ 24Vdc full continuous operation at maximal framespeed. When the Low Frequency Flat Field Correction is enabled the additional power dissipation is $\pm$ 0.7W		
Power connector	DIN1.0/2.3 CoaXPress Masterlink (figure 1)		





Figure 1: Quad CXP DIN1.0/2.3

- 1 Trigger in
- 2 Flash strobe out
- 3 Flash strobe return
- Trigger return



BINDER-09-3432-216-04

Figure 2: M12 I/O connector

#### Mechanical

Mounting	2 M4 mounting holes per side on camera front
Lensmount	4 x M3 at 60mm pitch - 50mm G7 reference (On request: F, M42, T2, TFLII, EF)
Outline	See figure 3
Weight	400g +/- 5% excl. lensmount




Figure 3: Mechanical outline

### **Sensor Mounting Accuracy**

XY-centering	± 0.050mm
Rotation	± 1mRad
Optical distance	4.526 ± 0.050mm
Perpendicularity	± 2mRad

### Compliance & Reliability

#### RoHS

2011/65/EU
2004/108/EC: EN61000-6-4 and EN61000-6-2
Contact discharge +/- 4 kV; Air discharge +/- 8 kV
In accordance with IPC-J-STD-001 class 3 and inspected according IPC-A-610C class 2
> 75,000h @ 30°C

S-25A80-Gx/CXP Issue 2.0 Revision 1.1

#### **Environmental**

#### Operating

Temperature	0°C to +30°C or max housing temp 50°C		
Humidity (relative)	20% - 80% non-condensing		
Shock	10 g, half sine shape, 6-10ms duration		
Vibration	3 g sinusoidal vibration sweeps 5 - 150 Hz		
Storage			
Temperature	-25°C to +65°C		
Humidity (relative)	5% - 95% non-condensing		
Shock	25 g, half sine shape, 6-10ms duration		
Vibration	10 g sinusoidal vibration sweeps 5 - 150 Hz		

Camera Types	Interface connector	I/O connector	Sensor	Type	Max. fps @ Full resolution
S-25A80-Gm/CXP-6-2.0	4 x DIN1.0/2.3	M12 4p	NOIP1SN025KA-GDI	Mono	84+ fps
S-25A80-Gc/CXP-6-2.0	4 x DIN1.0/2.3	M12 4p	NOIP1SE025KA-GDI	Raw Bayer	84+ fps
S-25A80-Gm/CXP-6-S10-2.0	4 x DIN1.0/2.3	M12 4p	NOIP1FN025KA-GDI	NIR (Mono)	84+ fps

#### Adimed

Adimec is the leading supplier of high-end cameras for machine vision, medical and outdoor imaging applications. Our Adimec True Accurate Imaging® technology forms the foundation for a broad range of camera products, and brings new levels of precision and accuracy to vision systems.

#### Custom cameras

Adimec has the ability to offer additional camera functionality and create customer specific cameras even for small volume programs. Built from platforms, our standard line of cameras give us a flexible base that can be tailored to fit your specifications. Contact us to discuss these options in more detail. Visit: <a href="https://www.adimec.com">www.adimec.com</a> for product details.



For maximum image quality, performance, and reliability in demanding applications - Choose Adimec

North America
Phone: (+1) 781-279-0770
Fax: (+1) 781-279-0771

Europe (+31) 40-2353900 Japan & Korea (+81) 3-5968-8377 (+81) 3-5968-8388 salesjp@adimec.com

Asia - Pacific (+65) 6334-1236 (+65) 6334-1436 salesan@adimec.co China (+86)21 6266 1692

 Fax:
 (+1) 781-279-0771
 (+81) 3-5968-8388
 (+65) 6334-1436

 E-mail
 salesus@adimec.com
 salesip@adimec.com
 salesap@adimec.com
 salesap@adimec.com

